

Socket enclosure

STG 024



STG 024

Socket enclosure

CUSTOMIZABLE

Productnumber: 73222401

Dimensions: 250 x 200 x 122 mm

Socket enclosure, protection class IP44, with integrated, pre-wired sockets, high mechanical resilience, non-sensitive to temperature, combinable, halogen-free

Cable insertions:

Top: Pre-embossing 8 x M20, 2 x M20/25, 1 x M32/40

Bottom: Pre-embossing 8 x M20, 2 x M20/25, 1 x M32/40

Left: Pre-embossing 2 x M20

Right: Pre-embossing 2 x M20

Rear: Pre-embossing 2 x M20/25

equipped with:

- 4 x SCHUKO® plug socket (on front), 230V
- 2 x CEE plug socket outlet (on front) 16A, 400V

Accessories supplied:

Attachment bushes: 2x M25, 2x M32, sealing plugs



Technical Data

Built-in devices

SCHUKO® plug socket (on front), 230V:	4
CEE plug socket outlet (on front) 16A, 400V:	2

electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP44
Number of rows:	0

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	250 mm
Length:	200 mm
Height:	122 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall mounting
Impact strength:	IK08

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Polycarbonate, glass-fibre reinforced
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

Cable gland

