

Home - Fischerelektronik - LA 35

 fischerelektronik.de/web_fischer/en_GB/VA/LA3510012/datasheet.xhtml

Features

width: 160.6 mm

height: 83 mm


length: 100 mm

thermal resistance: 0.13 - 0.048 K/W

surface:

- raw degreased aluminium (by the metre raw aluminium)
- mounting area(s) milled flat

Technical Drawing



Fan

type: ebmpapst 8212 JH4

dimensions: 80x80x38 mm

tension: 12 V DC

power inout: 39 W

max. air volume: 222 m³/h

temperature range: -20°C... +70°C

speed: 14,000 min⁻¹

noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)
type:	ebmpapst 8218 JH4
dimensions:	80x80x38 mm
tension:	48 V DC
power inout:	36 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C
speed:	14,000 min ⁻¹
noise level:	71 dB(A)
weight:	200 g
failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)
type:	ebmpapst 8214 JH4
dimensions:	80x80x38 mm
tension:	24 V DC
power inout:	38 W
max. air volume:	222 m ³ /h
temperature range:	-20°C... +70°C

speed:	14,000 min ⁻¹
--------	--------------------------

noise level:	71 dB(A)
--------------	----------

weight:	200 g
---------	-------

failure rate (L ₁₀):	L ₁₀ > 50,000 h (40°C)
----------------------------------	-----------------------------------

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de