


Home - Fischerelektronik - LA V 17

 fischerelektronik.de/web_fischer/en_GB/VA/LAV17400230/datasheet.xhtml




Cooling aggregates>Cooling aggregates with axial fan

122 x 120 mm, with axial fan and air-flow chamber

Features

width:	122 mm
height:	120 mm
length:	400 mm
thermal resistance:	0.092 - 0.046 K/W
surface:	• raw degreased aluminium (by the metre raw aluminium) • mounting area(s) milled flat
operating voltage of the fan motor:	• 24 V DC • 230 V AC

Technical Drawing



Fan

type: ebmpapst 4184NXH

dimensions: 119x119x38 mm

tension: 24 V DC

power inout: 11 W

max. air volume: 237 m³/h

temperature range: -30°C ... +70°C

speed: 4,400 min⁻¹

noise level: 57 dB(A)

weight: 390 g

failure rate (L₁₀): L₁₀ > 70,000 h (40°C)

type: ebmpapst 4656N

dimensions: 119x119x38 mm

tension:	230 V AC
power inout:	19 W
max. air volume:	160 m ³ /h
temperature range:	-40°C... +85°C
speed:	2,650 min ⁻¹
noise level:	47 dB(A)
weight:	550 g
failure rate (L ₁₀):	L ₁₀ > 37,500 h (40°C)

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de