




07502010

Profile Enclosure NoVoTronic

126 x 49 x 120 mm

Profile Enclosure NoVoTronic 126 x 49 x 120 mm

[Catalogues](#)[Assembly instructions](#)[Declaration of Conformity](#)[3D Data](#)

Technical data

Höhe	126 mm
Breite	49 mm
Tiefe	120 mm
Enclosure material	Gehäuseprofil: DIN EN 573 EN AW-AlMgSi, Gehäusedeckel: DIN EN 1706 EN AC-AISI 12 (Fe)
Colour Electronic Enclosure	Powder coating, Enclosure RAL 9005, jet black, function slide-in strips RAL 3003, ruby red
Ingress protection	IP65
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	90 °C

Commercial data

Order unit	1 Piece
Customs tariff number	76169990
Weight	0.55 kg
GTIN	4250157902115

ETIM classification

ETIM 8	EC001031
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

	07509004 Wall holder P100		07509007 Foot / connection element 100
	07509011 Wall profile 80/100 - 100		07509012 Wall profile 80/100 - 160
	07509013 Wall profile 80/100 - 200		83900003 Battery insert unit 9V block
	83900006 Battery insert unit 4x AA cells		