



21202590

ABS Enclosure Cabinet

200 x 250 x 150 mm

ABS Enclosure Cabinet 200 x 250 x 150 mm

[Catalogues](#)[Declaration of Conformity](#)[3D Data](#)

Technical data

Höhe	200 mm
Breite	250 mm
Tiefe	150 mm
Material	ABS
Colour	Light grey (RAL 7035)
Ingress protection	IP65
Degree of protection norm	EN 60529
Impact strength	IK08
temperature min.	-40 °C
temperature max.	60 °C
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	$4 \times 10^{15} \Omega \text{m}$
Surface resistance norm	IEC 60093
Special colours on request	Yes
Approvals	Maritime Register, UL 508A

Commercial data

Order unit	1 Piece
Customs tariff number	39269097
Weight	0.74 kg
GTIN	4250157915436

ETIM classification

ETIM 8	EC000261
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011205
Mounting plate for 21.202500



10013101
Front plate for 21.202500



21620001
Standard handle for Polyester cabinets



21620002
Standard handle with lock for Polyester
cabinets



21620003
Triangular lock for Polyester cabinets



21620004
Square lock for Polyglas (8mm)