



25163609

Aluminium Ex Enclosure Ex empty

160 x 360 x 91 mm

Aluminium Ex Enclosure Ex empty 160 x 360 x 91 mm

[Drawing](#)[3D Data](#)

Technical data

Höhe	160 mm
Breite	360 mm
Tiefe	91 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	90 °C
Seal material	VMQ-(silicone)
Other versions on request	EMV, SBG, SWB, SBGL
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEx, INMETRO, ISCVE Ukraine, UL Ex

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	2.63 kg
GTIN	4250157915955

ETIM classification

ETIM 8	EC002503
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011012
Mounting plate for 01.163609



10022001
HINGE INTERNAL / STEEL



10027001
HINGE EXTERNAL / GREY



10061425
DIN rail 35/7,5 for xx.163609