




25233311

Aluminium Ex Enclosure Ex empty

230 x 330 x 111 mm

Aluminium Ex Enclosure Ex empty 230 x 330 x 111 mm

[Drawing](#)[3D Data](#)

Technical data

Höhe	230 mm
Breite	330 mm
Tiefe	111 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	90 °C
Seal material	VMQ-(silicone)
Other versions on request	EMV, SBG, SWB, SBGL
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEx, INMETRO, ISCVE Ukraine, UL Ex

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	3.51 kg
GTIN	4250157916037

ETIM classification

ETIM 8	EC002503
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011017

Mounting plate for 01.233311



10022001

HINGE INTERNAL / STEEL



10027001

HINGE EXTERNAL / GREY



10061432

DIN rail 35/7,5 for xx.233311