



25141409

Aluminium Ex Enclosure Ex empty

140 x 140 x 91 mm

Aluminium Ex Enclosure Ex empty 140 x 140 x 91 mm

[Drawing](#)[3D Data](#)

Technical data

Höhe	140 mm
Breite	140 mm
Tiefe	91 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-55 °C
temperature max.	90 °C
Seal material	VMQ-(silicone)
Other versions on request	EMV, SBG, SWB, SBGL
Approvals	ABS, ATEX, CCOE India, EAC (TR CU), EXPLOLABS, IECEx, INMETRO, ISCVE Ukraine, UL Ex

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	1.3 kg
GTIN	4250157915917

ETIM classification

ETIM 8	EC002503
--------	----------

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



10011027

Mounting plate for 01.141409



10027001

HINGE EXTERNAL / GREY



10061454

DIN rail 35/7,5 for 01.141409