

IEC320-C7 (EU)

Country of Origin	China
RoHS	yes
Application	For Class II. Appliances
Approvals	ENEC

Length/cord		1.8m / 2x0.75mm2
Plug		SP-021A 2,5A/250V
Connector		IS-033 2,5A/250V
Rating		300/300V 70°C
Flex cord		H03VVH2-F
WEIGHT / PACKING	1pc	N.W.: 82 g / pc
	BOX	200 pcs / 1box
		G.W.: 17,3 kg / box
		0.55x0.36x0.20 [m]



Available also in white version

IEC320-C7 (UK)

Country of Origin	China
RoHS	yes
Application	For Class II. Appliances
Approvals	ASTA, Singapore, ENEC

Length/cord		1.8m / 2x0.75mm2
Plug		SP-62 5A/250V
Connector		IS-033 2,5A/250V
Fuse		5A
Rating		300/300V 70°C
Flex cord		H03VVH2-F
WEIGHT / PACKING	1pc	N.W.: 146 g / pc
	BOX	100 pcs / 1box
		G.W.: 14,6 kg / box
		0.55x0.36x0.20 [m]



IEC320-C7 (USA)

Country of Origin	China
RoHS	yes
Application	For Class II. Appliances
Approvals	UL, CSA

Length/cord		1.8m / 2x0.75mm2
Plug		SP-12N 7A/125V
Connector		IS-033 7A/125V
Rating		300V 105°C
Flex cord		SPT-1
WEIGHT / PACKING	1pc	N.W.: 71 g / pc
	BOX	200 pcs / 1box
		G.W.: 14,7 kg / box
		0.55x0.36x0.20 [m]



IEC320-C7 (Aus)

Country of Origin		China
RoHS		yes
Application		For Class II. Appliances
Approvals		SAA
Length/cord		1.8m / 2x0.75mm ²
Plug		SP-501A 7,5A/250V
Connector		IS-033 2,5A/250V
Rating		300/300V 70°C
Flex cord		H03VVH2-F
WEIGHT / PACKING	1pc	N.W.: 92 g / pc
	BOX	125 pcs / 1box
		G.W.: 12,4 kg / box
		0.55x0.36x0.20 [m]



IEC320-C7 (Japan)

Country of Origin		China
RoHS		yes
Application		For Class II. Appliances
Approvals		PSE
Length/cord		1.8m / 2x0.75mm ²
Plug		SP-18B 7A/125V
Connector		IS-033C 7A/125V
Rating		300V 60°C
Flex cord		VCTFK
WEIGHT / PACKING	1pc	N.W.: 104 g / pc
	BOX	150 pcs / 1box
		G.W.: 16,3 kg / box
		0.55x0.36x0.20 [m]

