


Product data sheet

Cable



Product description	Contacts: 5 wires, shielded, Standard, PUR, black (RAL 9005), 5 x 0.25 mm², 100 m
Area	Shielded cable
Part no.	08 3096 000 000

Illustration



Technical data

General features

Part no.	08 3096 000 000
	Alternative part no.: 52 0268 000
Cable length	100 m (Other lengths are available on request.)
Version	Raw cable
Weight (g)	4115.00
Customs tariff number	85444995
Country of Origin	DE

Electrical parameters

EMC compliance	shielded
----------------	----------

Material

REACH SVHC	None (No pollutants)
SCIP number	SCIP-number not available

Classifications

eCl@ss 11.1	27-44-01-90
ETIM 9.0	EC002638

Cable data - Structure of the cable

Cable type	Standard
Cable diameter	4.8 mm

Product data sheet

Cable



Product description	Contacts: 5 wires, shielded, Standard, PUR, black (RAL 9005), 5 x 0.25 mm², 100 m
Area	Shielded cable
Part no.	08 3096 000 000

Cross section	5 x 0.25 mm²
Sheath material	PUR
Single-lead insulation	PP
Single-lead structure	32 x 0.10 mm
Cable color	black (RAL 9005)

Cable data - Electrical properties

Operating voltage	250 V effective
Cable test voltage	2000 V effective
Conductor resistance	75 Ω/Km (20°C)

Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	> 2 million
Permitted acceleration	5 m/s²
Travel speed	at 5 m horizontal path -> 200 m/min

Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 90 °C
Temperature range cable fixed from/to	-50 °C / 90 °C

Cable data - Other features

Halogen free	yes
--------------	-----