



New version 2019, Efest SLIM K1 charger comes with novel 7 languages packaging & user manual ! Lightweight and practical, fashion and convenient !



SLIM

K1

Compatible With Lithium
IMR 3.6V/3.7V Batteries:

- | | |
|-------|-------|
| 10440 | 18500 |
| 14500 | 18650 |
| 16340 | 26500 |
| 17340 | 26650 |
| 18350 | 20700 |
| 18490 | 21700 |

AC input Power ----- AC 100~240V 50/60Hz
 DC input power ----- DC 5V 1A
 DC output Power ----- DC 5V 1A
 1*1A CC current ----- 1000mA±10%
 Auto cut-off voltage ----- 4.20±0.05V
 CV cut-off current ----- <100mA
 Standby current ----- <20mA
 Activation current ----- 50mA~100 mA
 Auto recharge voltage ----- 4.10±0.10V
 Operation Temperature ----- 0℃ ~ 40℃
 Storage Temperature ----- -40℃ ~ +70℃



CONVENIENT CHARGING FOR ANYWHERE YOU WANT AND ANYTIME YOU NEED.

DESCRIPTION

Efes SLIM K1 USB Charger

- Stylish & eye catching design
- Incredibly lightweight and conveniently portable
- Safe and handy 5V 1A USB charger



FEATURES

- Fast charging mode: 1.0A
- Reverse polarity protection
- Activation function
- Auto-detect charging function
- Over-charging protection
- Short circuit protection



CRAFTSMANSHIP

- Spring made by piano wire, it provides a smooth sliding action when installing and removing batteries
- Steel cathode with low resistance and hard chromium plating processing to achieve a more precise charging voltage
- 15,000+ times spring testing quality warranty



CERTIFICATIONS



Global Insurance technical support with
FCC,CE,RoHS certification.

