



Compatible With Lithium
IMR 3.6V/3.7V Batteries:

10440	18500
14500	18650
16340	26500
17340	26650
18350	20700
18490	21700

AC input Power	----- AC 100~240V 50/60Hz
DC input power	----- DC 5V 2A
DC output Power	----- DC 5V 2A
2*1A CC current	----- 1000mA $\pm$ 10%
Auto cut-off voltage	----- 4.20 $\pm$ 0.05V
CV cut-off current	----- <100mA
Standby current	----- <20mA
Activation current	----- 50mA~100 mA
Auto recharge voltage	----- 4.10 $\pm$ 0.10V
Operation Temperature	----- 0 $^{\circ}$ C ~ 40 $^{\circ}$ C
Storage Temperature	----- -40 $^{\circ}$ C ~ +70 $^{\circ}$ C



CONVENIENT CHARGING FOR ANYWHERE YOU WANT AND ANYTIME YOU NEED.

DESCRIPTION

Efest SLIM K2 USB Charger

- Stylish & eye catching design
- High quality fire retardant material
- Incredibly lightweight and conveniently portable





FEATURES

- Fast charging mode: 1.0A (4.2V 2pcsX1.0A)
- Reverse polarity protection
- Activation function
- Auto- detect charging function
- Over- charging protection
- Short circuit protection



CRAFTSMANSHIP

- Spring made by piano wire, it provides a smooth sliding action when installing and removing batteries.
- Steel cathode with low resistance and hard chromium plating processing to achieve a more precise charging voltage.
- 15,000+ times spring testing quality warranty

CERTIFICATIONS



Global Insurance technical support with
FCC,CE, RoHS certification.



PACKAGE

Newest 7 Languages Version
(EN/DE/FR/IT/ES/RU/JA)

WARNING

