



LUSH

Q2

Compatible With Lithium
IMR 3.6V/3.7V Batteries:

10440

18490

14500

18500

16340

18650

17340

26500

18350

26650

AC input power ----- AC 100~240V 50/60Hz

1*2.0A CC current ----- 2000mA $\pm$ 10%

2*1.0A CC current ----- 1000mA $\pm$ 10%

Auto cut-off voltage ----- 4.20 $\pm$ 0.05V

CV cut-off current ----- < 10% max

Standby current ----- <10.0mA

Activation current (battery voltage<2.90V) ----- 10mA~50 mA

Auto recharge voltage ----- 4.10 $\pm$ 0.10V

Operation Temperature ----- 0°C ~ 40°C

Storage Temperature ----- -40°C ~ +70°C



CONVENIENT CHARGING FOR ANYWHERE YOU WANT AND ANYTIME YOU NEED.



DESCRIPTION
Efest LUSH Q2 LED Indicator Charger

- Fashion, modern and curve appearance
- Stylish & eye catching packaging
- High quality fire retardant material

FEATURES

- Fast charging, auto-select between 1.0A and 2.0A
- Auto stop when fully charged & auto recharge when voltage lower than 4.05V
- 4 kinds of protection over-discharging, over-voltage, short circuit and reverse polarity protection
- The batteries at or over 0.6V can be activated by Q2
- Battery slot monitors independently



CRAFTSMANSHIP

- Spring made by piano wire, it provides a smooth sliding action when installing and removing batteries
- Steel cathode with low resistance and hard chromium plating processing to achieve a more precise charging voltage
- 15,000+ times spring testing quality warranty



CERTIFICATIONS



Global Insurance technical support with FCC,CE,RoHS certification.



PACKAGE

WARNING

