



Compatible With Lithium
IMR 3.6V/3.7V Batteries:

10440	18500
14500	18650
16340	26500
17340	26650
18350	20700
18490	21700

AC input power	AC 100~240V 50/60Hz
1*2.0A CC current	2000mA±10%
2*1.0A CC current	1000mA±10%
4*0.5A CC current	500mA±10%
Auto cut-off voltage	4.20±0.05V
CV cut-off current	< 10% max
Standby current	<10.0mA
Activation current (battery voltage<2.90V)	10mA~50 mA
Auto recharge voltage	4.10±0.10V
Operation Temperature	0°C ~ 40°C
Storage Temperature	-40°C ~ +70°C



CONVENIENT CHARGING FOR ANYWHERE YOU WANT AND ANYTIME YOU NEED.



DESCRIPTION

Efest LUSH Q4 LED Indicator Charger

- Fashion, modern and curve appearance
- Stylish & eye catching packaging
- High quality fire retardant material

FEATURES

- Three charging modes: 2.0A 1.0A 0.5A
- Auto-stop when fully charged & auto-recharge when voltage lower than 4.05V
- 4 kinds of protection over- discharging, over- voltage, short- circuit and reverse polarity protection
- The batteries at or over 0.6V can be activated by Q4 charger
- Battery slot monitors independently



CRAFTSMANSHIP

- Spring made by piano wire, it provides a smooth sliding action when installing and removing batteries.
- Steel cathode with low resistance and hard chromium plating processing to achieve a more precise charging voltage.
- 15,000+ times spring testing quality warranty



CERTIFICATIONS



Global Insurance technical support with
FCC,CE,RoHS certification.

PACKAGE

Newest 7 Languages Version
(EN/DE/FR/IT/ES/RU/JA)

WARNING

