



Compatible With Lithium
IMR 3.6V/3.7V Batteries:

10440	18500
14500	18650
16340	26500
17340	26650
18350	20700
18490	21700

Input power	-----DC 5V 2A
2*1A CC current	----- 2000mA±10%
1*1A CC current	----- 1000mA±10%
4*0.5A/3*0.5A CC current	----- 500mA±10%
Auto cut-off voltage	----- 4.20±0.05V
CV cut-off current	----- <100mA
Standby current	----- <20mA
Activation current	----- 50mA~100 mA
Auto recharge voltage	----- 4.10±0.10V
Operation Temperature	----- 0℃ ~ 40℃
Storage Temperature	----- -40℃ ~ +70℃



HIGH QUALITY ABS FIRE-RETARDANT MATERIAL& ELECTRONIC COMPONENT

LED INDICATOR DESCRIPTION

Efest SLIM K4 USB Charger

- After insert the battery to the slot correctly, SLIM K4 will charge the battery automatically in few seconds.
- Indicator in standby mode/fully charged turns blue color, white color while in charging.





FEATURES

- Auto detect charging current: 2×1.0A/ 1×1.0A /4×0.5A/3×0.5A
- Safe charging mode: CC & CV
- Safe and convenient USB charger (5V 2A)
- Monitors and charges each slot independently
- Low voltage smart activation recovery function
- Incredibly lightweight and conveniently portable



CRAFTSMANSHIP

- Spring made by piano wire, it provides a smooth sliding action when installing and removing batteries.
- Steel cathode with low resistance and hard chromium plating processing to achieve a more precise charging voltage.
- 15,000+ times spring testing quality warranty



USB PORT DESIGN

Type-C USB port reduce the heat of the port effectively



6

Protection Levels Built-in Intelligent Protection Chip

1. Short circuit protection
2. Automatic over-charging protection
3. Automatic over-discharging protection
4. Reverse polarity protection
5. 0V activation recovery function
6. Hardware and software double protection

CERTIFICATIONS



Global Insurance technical support with
FCC, CE, RoHS certification.



PACKAGE

Newest 7 Languages Version
(EN/DE/FR/IT/ES/RU/JA)

WARNING

