

54113002	DATA SHEET	
Valid from: 20.12.2023	SKINTOP® SDV-M ATEX / SDVR-M ATEX	

The SKINTOP® SDV-M ATEX / SDVR-M ATEX are sealing inserts to be used with the cable glands SKINTOP® MS-M ATEX / MSR-M ATEX or SKINTOP® K-M ATEX / KR-M ATEX in explosion endangered areas. These sealing inserts close and seal SKINTOP® MS-M ATEX / MSR-M ATEX or SKINTOP® K-M ATEX / KR-M ATEX cable glands which are not yet equipped with cables.



Technical features:

Material	CR	
Sizes	SDV-M	M12 up to M63
	SDVR-M	M16 up to M32
Colour	Black	
Protection class	IP66, IP68 – 10 bar, test acc. to EN 60529	
Temperature range	-30 °C up to +70 °C	
UV resistance	acc. to DIN EN ISO 4892-3	

Certifications:



Condition of certifications:


The sealing plugs SKINTOP® SDV-M ATEX / SDVR-M ATEX may only be used in combination with the appropriate cable glands SKINTOP® MS-M ATEX / MSR-M ATEX or SKINTOP® K-M ATEX / KR-M ATEX.

Norm references:



Creator: M. Jurak /PDP Released: DAMU1/PDP	Document: DB54113002EN Version: 04	Page 1 of 2
---	---------------------------------------	-------------

54113002	DATA SHEET	
Valid from: 20.12.2023	SKINTOP® SDV-M ATEX / SDVR-M ATEX	



SKINTOP® SDV-M ATEX

Article designate	Ø A [mm]	Ø B [mm]	C [mm]	D [mm]	Article No.
SDV-M12 ATEX	10,5	5,8	12,5	9,5	54113002
SDV-M16 ATEX	13,5	9,3	13	10	54113012
SDV-M20 ATEX	18	12,5	14,5	11	54113022
SDV-M25 ATEX	21	16,5	15,5	12	54113032
SDV-M32 ATEX	26	20,5	19	15	54113042
SDV-M40 ATEX	33	27,5	22	18	54113052
SDV-M50 ATEX	40,5	35	27,5	23	54113062
SDV-M63 ATEX	51	44,5	31,5	27	54113072

SKINTOP® SDVR-M ATEX

Article designation	Ø A [mm]	Ø B [mm]	C [mm]	D [mm]	Article No.
SDVR-M16 ATEX	13,5	6,3	14	10	54113013
SDVR-M20 ATEX	18	9,3	16	11	54113023
SDVR-M25 ATEX	21	12,3	17	12	54113033
SDVR-M32 ATEX	26	14,3	20,5	15	54113043

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: M. Jurak /PDP Released: DAMU1/PDP	Document: DB54113002EN Version: 04	Page 2 of 2
---	---------------------------------------	-------------