

EXTERNAL M.2 SSD NVME ENCLOSURE



PLUG & PLAY



HIGH SPEED



INTELLIGENT
SLEEP



PORTABLE



EN TECHNICAL SPECIFICATION

Interface:	USB 3.0
Maximum bandwidth:	10 Gbps
Maximum capacity of the installed disk:	4 TB
Connector:	USB 3.1 Gen 2
Dimensions:	104.5 × 39.5 × 12 mm
Weight:	44 g
Colour:	grey
Supported drives:	M.2 2230, M.2 2242, M.2 2260, M.2 2280
Compatible with:	Windows XP/Vista/7/8/10/11/MacOS/Linux

