

INDUCTION CHARGER 15 W

15W

MAXIMUM
OUTPUT
POWER



COMPACT
SIZE



INDUCTION
TECHNOLOGY



STANDARD



EN TECHNICAL SPECIFICATION

Input voltage:	12 V= 2 A, 9 V= 2 A, 5 V= 2 A
Output power:	15 W / 10 W / 7.5 W / 5 W
Efficiency:	≥ 73%
Transmission distance:	≤ 8 mm
Standard:	Qi
Protection:	overcurrent, short circuit protection
Colour:	black
Size:	99 × 99 × 5 mm
Weight:	50 g
Compatible with all devices with Qi function.	

