



Data sheet Product SK 06 G

- [Print data sheet](#)
- [Recommend page](#)



Sockets>High-precision contacts, loose

Female contacts for Ø 0.5 mm, round contact

Features

contact material:	CuZn-alloy
-------------------	------------

contact spring:	gold-plated
-----------------	-------------

surface contact / contact sleeve:	• Ni+$\geq 0.2\mu\text{m}$ Au • Ni+4...6μm Sn
--------------------------------------	--

inner contact spring material:	CuBe-alloy
--------------------------------	------------


inner contact spring surface:	Ni+0,75 μm Au
-------------------------------	--------------------------

insert depth:	2.5...3.6mm
---------------	-------------

insertion / drawing force:	• 1.8 N/1.4 N • 4 lamellas contact
----------------------------	--

type:	female
nominal current:	1.5 A
nominal voltage:	60 V DC
test voltage:	1000 V
plug-in cross-section:	0,22x0,25mm ...0,40x0,55mm
surface of contact:	gold-plated
connection type:	THT (soldering)
grid:	2.54 mm

Technical Drawing



Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
58511 Lüdenscheid

Telefon +49 2351 435-0
Telefax +49 2351 45754

info@fischerelektronik.de
www.fischerelektronik.de