

## **ESD PICKING BINS**

**25-304-20xx**



### **Products Specifications**

|                     |                                    |
|---------------------|------------------------------------|
| Material:           | Conductive polypropylene copolymer |
| Colour:             | Black                              |
| Density (at 23°C):  | 1.04 g/cm <sup>3</sup>             |
| Use of temperature: | +60/-20°C                          |
| Surface resistance: | < 10 <sup>4</sup> Ω                |
| Compliance:         | IEC 61340-5-1                      |

### **Part-Numbers and Dimensions**

| Part Numbers | External Dimensions DxWxH (mm) | Internal Dimensions DxWxH (mm) | Capacity (liter) | Weight (gr) |
|--------------|--------------------------------|--------------------------------|------------------|-------------|
| 25-304-2001  | 95 x 105 x 55                  | 63 x 91 x 44                   | 0.25             | 42          |
| 25-304-2002  | 170 x 100 x 75                 | 132 x 88 x 65                  | 1                | 90          |
| 25-304-2003  | 230 x 150 x 125                | 191 x 127 x 110                | 3.8              | 248         |
| 25-304-2006  | 350 x 210 x 145                | 270 x 180 x 130                | 9.4              | 678         |
| 25-304-2005  | 350 x 210 x 200                | 270 x 180 x 180                | 12.5             | 848         |
| 25-304-2007  | 500 x 310 x 145                | 282 x 425 x 134                | 20               | 1222        |
| 25-304-2004  | 500 x 310 x 200                | 425 x 282 x 183                | 28               | 1534        |
| 25-304-2008  | 500 x 310 x 300                | 282 x 425 x 285                | 42               | 1874        |