

1933IH

High-power die grinder

CE

- Collect chuck, Ø 3 mm and 6 mm

Free speed	20,000 rpm
Chuck capacity	3 - 6 mm
Power	0.75 kW
Air inlet	1/4" GAS
Working pressure	6.2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	370 l/min
Weight	800 g

	art.	 g
019330006	1933IH	800

