

Scapa 2702

PVC Premium Electrical Adhesive Tape - 0.13mm

DESCRIPTION

Scapa 2702 is a 0.13mm premium quality, electrical self-extinguishing soft PVC tape that uses an aggressive pressure sensitive rubber-based adhesive system. It has been designed for use where a recognised specification or international standard is required and where environmental safety is a concern.

APPLICATIONS

- Hand application
- Primary electrical insulation
- Harnessing
- Protection for low and medium voltage cable splices
- Colour coding

PRODUCT BENEFITS

- Good resistance to abrasion, corrosion and moisture
- High dielectric strength and good mechanical protection
- Outstanding conformability
- Tape can be applied at low temperature (till -10°C)
- IMQ and VDE Approval Certificates according to IEC 60454-3-1
- Conforms to the European Directive 2011/65/EC (RoHS 2) and Commission Delegated Directive (EU) 2015/863 (RoHS 3)
- Index temperature 0°C to 90°C
- UL 510A - Recognized Tape OANZ2 : File E509583

Accreditation:

Conforms to the technical requirements of BS4J10/BSEN60454

TECHNICAL PROPERTIES

Technical Property	Nominal Value	Unit	Test Method
Thickness	0.13	mm	IEC 60454-2
Tensile Strength	25	N/cm	IEC 60454-2
Elongation at Break	180	%	IEC 60454-2
Adhesion to Steel	1.8	N/cm	IEC 60454-2
Adhesion to Backing	1.8	N/cm	IEC 60454-2
Dielectric Strength	40	kV/mm	IEC 60454-2
Flammability	Self extinguishing	-	IEC 60454-2

STANDARD PRESENTATIONS

- Roll Length: 10, 20, 25 and 33metres
- Roll Width: 12, 15, 19 and 25mm. Also some colours in 50mm
- Core: 32mm Scapa branded cardboard core
- Packaging: Cellowrapped with Scapa label and bar code
- Colours: Black, White, Grey, Red, Blue, Yellow, Dark green, Light Green, Brown, Orange, Violet, Transparent, Yellow/green

Note:

RECOMMENDATIONS

Rolls should be stored flat on their cut edges in the original packaging. The product must be protected from dust, heat, moisture, direct sunlight and solvent fumes. The storage temperature should be between +5°C and +25°C. Use within 24 months from the date of manufacturing

The tape should be applied with sufficient tension to ensure an optimum bonding and a minimum of two layers with a half overlap. The final layer should be wrapped with a lower tension to prevent flagging effects.

Surfaces should be clean, dry and free of dust, grease, oil or other contaminants.