


ROCKER SWITCH MODEL MR2 SERIES




RATING:16(8)A 125/250V~T55 (cURus/ENEC15)

DIELECTRIC VOLTAGE-WITHSTAND:1,500VAC FOR 1 MINUTE

INSULATION RESISTANCE:DC 500V 100MΩ (MIN.)

CONTACT RESISTANCE:20mΩ INITIAL (MAX.)

WATERPROOF GRADE:IP68



X(PANEL THICKNESS)	Y(CUTOUT DIMENSION)	Z(CUTOUT DIMENSION)
0.75~1.25mm	19.2 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₋₀ mm
1.25~2mm	19.4 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₋₀ mm
2~3mm	19.8 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₋₀ mm

PANEL CUTOUT DIMENSION TABLE

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED:±.012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES			ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	MR2 SPEC DRAWING	DWG NO	
			DRAWN BY	楊偉韶	DESIGNED BY	蔡劍	SCALE	2/1		PART NO		MR2-110C5W-NBBQ-29NC	S8164A
			CHECKED BY		APPROVED BY		DATE	2020.08.13		PART NO			
 2020.08.13	首次出圖	楊偉韶											