

**6200**

# HPX 6200 REPAIR TAPE



- Very strong, universal, high quality cloth tape with high adhesive strength
- Suitable for securing and repairing pipes, tubes, garden hoses, etc.
- Hand tearable
- Waterproof and weather resistant

| Art. No. | width  | length | colour      | Pack. | EAN code      |
|----------|--------|--------|-------------|-------|---------------|
| CS5010   | 48 mm  | 10 m   | silver      | 12    | 5425014220537 |
| CB5010   | 48 mm  | 10 m   | black       | 12    | 5425014220513 |
| CS5025   | 48 mm  | 25 m   | silver      | 30    | 8711347114610 |
| CB5025   | 48 mm  | 25 m   | black       | 30    | 8711347114573 |
| CW5025   | 48 mm  | 25 m   | white       | 30    | 5425014220018 |
| CY5025   | 48 mm  | 25 m   | yellow      | 30    | 5425014220674 |
| CR5025   | 48 mm  | 25 m   | red         | 30    | 5425014220681 |
| CL5025   | 48 mm  | 25 m   | light blue  | 30    | 5425014220698 |
| CD5025   | 48 mm  | 25 m   | dark blue   | 30    | 5425014220704 |
| CG5025   | 48 mm  | 25 m   | olive green | 30    | 5425014220711 |
| CS5050   | 48 mm  | 50 m   | silver      | 18    | 8711347114634 |
| CB5050   | 48 mm  | 50 m   | black       | 18    | 8711347114597 |
| CS7550   | 75 mm  | 50 m   | silver      | 12    | 5425014224665 |
| CB7550   | 75 mm  | 50 m   | black       | 12    | 5425014224740 |
| CS10050  | 100 mm | 50 m   | silver      | 12    | 5425014224764 |
| CB10050  | 100 mm | 50 m   | black       | 12    | 5425014222975 |

**Adhesive:** natural rubber

**Carrier:** PE coated cloth

**Maximum temperature:** 60°C (up to 80°C for short periods)

**Tensile strength:** 183 N/25 mm

**Adhesive strength:** 13 N/25 mm

**Thickness:** 0,30 mm

**HPX**

Frankrijkstraat 8 | 9140 Temse | Belgium

T 0032 3 710 19 19 | F 0032 3 711 34 64 | [info@hpx.eu](mailto:info@hpx.eu) | [www.hpx.eu](http://www.hpx.eu)

