

DATASHEET

STANDARD CABLE TIES BLACK



INSTALLATION TEMPERATURE	-10°C ÷ 60°C
MOISTURE ABSORPTION	2,7% (23°C - 50% R.H.)
FIRE RESISTANCE OF MATERIAL	UL 94-V2 Halogen-free
RESISTANCE TO	aromatic solvents, oils, greases and their derivatives
RESISTANT	ultraviolet exposure
LIMITED RESISTANCE	acids
NON-RESISTANT	phenols and chlorinated solvents
WORKING TEMPERATURE	-40°C ÷ 85°C
MATERIAL	polyamide 6.6 natural + 1% carbon black

ITEM NO.	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
TT3X100B	2,5x100	black	22	80
TT3x150B	2,5x150	black	35	80
TT3X200B	2,5x200	black	50	80
TT3X250B	2,5x250	black	65	80
TT4X150B	3,6x150	black	35	178
TT4X200B	3,6x200	black	50	178
TT4X250B	3,6x250	black	65	178
TT4X300B	3,6x300	black	80	178
TT4X370B	3,6x370	black	100	178
TT5X200B	4,6x200	black	50	216
TT5X250B	4,6x250	black	65	216
TT5X300B	4,6x300	black	80	216
TT5X350B	4,6x350	black	90	216
TT5X400B	4,6x400	black	105	216
TT5X450B	4,6x450	black	120	216
TT5X500B	4,6X500	black	150	216
TT8X300B	7,6x300	black	80	540
TT8X400B	7,6x400	black	105	540
TT8X500B	7,6x500	black	150	540
TT9X650B	8,8x650	black	190	981
TT9X760B	8,8x760	black	225	981