

**8500**

AIRTIGHT FLEX



- Flexible, single sided, polyethylene tape for indoor use
- Airtight sealing of penetrations (e.g. cables, pipes, ...) and other connections
- Can be used for bonding and covering overlaps
- Sealing of joints of OSB and DWD panels
- Good adhesion to non-polar and low energy surfaces (LSE)
- Service temperature: until -10°C (ideally between 5°C and 35°C)
- DIN 4108/7 and DIN 4108/11
- EMICODE EC1 plus
- Contains no solvents

Art. No.	width	length	colour	Pack.	EAN code
IS5025	50 mm	25 m	green	30	5407004560076
IS6025	60 mm	25 m	green	24	5425014228465

Adhesive: acrylic

Carrier: polyethylene with reinforced scrim

Maximum temperature: -30°C - +100°C

Adhesive strength: 25 N/25 mm

Thickness: 0,25 mm

HPX

Frankrijkstraat 8 | 9140 Temse | Belgium

T 0032 3 710 19 19 | F 0032 3 711 34 64 | info@hpx.eu | www.hpx.eu

