




Section A-A



Section B-B



Section C-C

Specifications & Ordering Information:

Thickness	Material	Wire Range	Insulation O.D.	Finish	Qty/reel
0.2	Brass	AWG #22~28	1.6-1.2 mm	Pre. Tin-Plated	10,000PCS

RoHS
Compliant

Ninigi

APPD.
核准 BETTY

DWG.
製圖 BETTY

DATE 制表日
2009/08/14



SCALE
比例 參考

UNIT
單位 MM

TOLERANCE :
.000 : ± 0.08
.00 : ± 0.13
.0 : ± 0.25

SIZE.
紙張尺寸 A 4

PART NAME 品名
DUPOND 2.54mm TERMINAL BRASS MATERIAL
SUITABLE AWG22~28 1R=10K PCS
STANDARD TYPE (less than 1X14P & 2X7P use this type)

PART NO.
料號 NDR-T