



16M Series
Metric Nylon Flat Washers




- Specifications:
- Material: UL94 V-2 Nylon 6/6
 - Color: Natural

Item No.	ID mm	OD mm	Thickness mm	Fits Screw	Bulk Pack Qty
16M02050080	2.2	5.0	0.8	M2	1000
16M02556080	2.7	5.6	0.8	M2.5	1000
16M03080080	3.2	8.0	0.8	M3	1000
16M03580080	3.7	8.0	0.8	M3.5	1000
16M04080200	4.3	8.0	2.0	M4	1000
16M04090080	4.3	9.0	0.8	M4	1000
16M05011100	5.3	11.0	1.0	M5	1000

Item No.	ID mm	OD mm	Thickness mm	Fits Screw	Bulk Pack Qty
16M06012150	6.4	12.0	1.5	M6	1000
16M08018200	8.4	18.0	2.0	M8	500
16M08525200	8.5	25.0	2.0	M8.5	500
16M08535110	8.5	35.0	1.1	M8	1000
16M10022250	10.5	22.0	2.5	M10	500
16M12025200	13.4	25.1	2.5	M12	500
16M12034250	13.4	33.6	3.1	M12	1000
16M70074500	70.0	74.5	5.0	M64	1000

MFW/17M34815 Series
DIN 34815 / 125 Nylon Flat Washers



- Specifications:
- Material: UL94 V-2 Nylon 6/6
 - Color: See Table
- Features:
- Conforms to DIN 34815 / DIN 125

Item No.		ID	OD	Thickness	Fits	Bulk Pack
Natural	Black	mm	mm	mm	Screw	Qty
MFW010A	—	2.2	5.0	0.3	M2	1000
MFW020A	—	2.7	6.0	0.5	M2.5	1000
MFW030A	MFW030B	3.2	7.0	0.5	M3	1000
MFW040A	—	3.7	8.0	0.5	M3.5	1000
• 17M04DIN34815	• 17M04DIN34815B	4.3	9.0	0.8	M4	1000
• 17M05DIN34815	• 17M05DIN34815B	5.3	10.0	1.0	M5	1000
• 17M06DIN34815	• 17M06DIN34815B	6.4	12.0	1.6	M6	1000
• 17M08DIN34815	• 17M08DIN34815B	8.4	16.0	1.6	M8	1000
• 17M10DIN34815	• 17M10DIN34815B	10.5	20.0	2.0	M10	1000
• 17M12DIN34815	• 17M12DIN34815B	13.0	24.0	2.5	M12	500
MFW110A	—	15.0	30.0	3.0	M14	1000
• 17M16DIN34815	• 17M16DIN34815B	17.0	30.0	3.0	M16	1000
MFW130A	—	19.0	34.0	3.0	M18	250
• 17M20DIN34815	• 17M20DIN34815B	21.0	37.0	3.0	M20	500
MFW150A	—	25.0	44.0	4.0	M22	250
MFW160A	—	28.0	50.0	4.0	M24	250
MFW170A	—	31.0	56.0	4.0	M27	250
MFW180A	—	37.0	66.0	5.0	M30	250
MFW190A	—	40.0	72.0	6.0	M36	250

17M34816 Series
DIN 34816 / 9021 Nylon Flat Washers



- Specifications:
- Material: UL94 V-2 Nylon 6/6
 - Color: Natural
- Features:
- Conforms to DIN 34816 / DIN 9021

Item No.	ID mm	OD mm	Thickness mm	Fits Screw	Bulk Pack Qty
17M03DIN34816	3.2	9.0	0.9	M3	1000
17M04DIN34816	4.3	12.0	1.1	M4	1000
17M05DIN34816	5.3	15.0	1.4	M5	1000
17M06DIN34816	6.4	18.0	1.8	M6	1000
17M08DIN34816	8.4	24.0	2.2	M8	500
17M10DIN34816	10.5	30.0	2.7	M10	1000
17M12DIN34816	13.0	37.0	3.3	M12	500
17M16DIN34816	17.0	50.0	3.3	M16	1000