

DATASHEET

CABLE TIES
SOFT NATURAL



INSTALLATION TEMPERATURE	-10°C ÷ 60°C
MOISTURE ABSORPTION	2,7% (23°C - 50% R.H.)
FIRE RESISTANCE OF MATERIAL	UL 94-V2 Halogen-free
RESISTANCE TO	aromatic solvents, oils, greases and their derivatives
LIMITED RESISTANCE	acids
NON-RESISTANT	phenols and chlorinated solvents
WORKING TEMPERATURE	-40°C ÷ 85°C
MATERIAL	polyamide 6.6 natural

ITEM NO.	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
TT3.3X200	3,3x200	natural	50	167
TT3.3X250	3,3x250	natural	65	167
TT3.3X300	3,3x300	natural	80	167
TT4.3X200	4,3x200	natural	50	206
TT4.3X300	4,3x300	natural	80	206
TT4.3X400	4,3x400	natural	105	206