

12-in-1 USB-C Docking Station

Perfect for your laptop



DP+HDMI+VGA
Crystal Clear

100W PD
Quick Charging

Gigabit Ethernet Port
Stable and Fast

Massive Expansion



1 USB-C PD
fast charge
100W PD

2 VGA
1080P@60Hz

3 3.5mm audio port
Connect the
headphones/speaker

4 DP
4K@30Hz

5 HDMI
4K@30Hz

6 Gigabit Ethernet
port
1000Mbps

7 USB 3.0*2
5Gbps

8 USB-C Gen 1
5Gbps

9 SD/TF card slot
256G

10 USB 2.0
480Mbps

Note: All data are from Vention Lab.

MST Multiple Display Modes

It is equipped with DP, HDMI and VGA ports which support mirror mode and extend mode
Your perfect office and home assistant.

Display in different systems

Windows system



Mac OS system



Note: Mac OS does not support MST and the 3 external monitors will display the same content.

4K UHD, Enjoy the Visual Feast

The resolution of DP and HDMI ports are up to 4K@30Hz, VGA port is up to 1080P@60Hz.



Note: DP and HDMI interfaces support audio and video synchronous transmission, while VGA interface does not support the audio transmission.

Resolution of DP+HDMI+VGA Ports

Mac OS & Windows system

	DP	HDMI	VGA
Single Display	4K@30Hz	4K@30Hz	1080P@60Hz
Dual Display	4K@30Hz (Mac OS) 1080P@60Hz (Win)	4K@30Hz (Mac OS) 1080P@60Hz (Win)	
		1080P@60Hz	1080P@60Hz
	1080P@60Hz		1080P@60Hz
Triple Display	1080P@60Hz	1080P@60Hz	1080P@60Hz

Note: All data are from Vention Lab.

USB-C Fast Data Transmission

With USB-C Gen 1 interface, it supports USB-C hard disk, U disk and card reader

5Gbps

Note: All data are from Vention Lab.

Up to 100W PD Quick Charging


Power delivery (PD 3.0) up to 100W
upstream charging the laptop



Note: All data are from Vention Lab.

Maximize Your Work Efficiency

2*super speed USB 3.0 ports
and 1*USB 2.0 port are better for mouse
keyboard, U disk and other devices.



Mouse



Keyboard



U disk



Mobile hard
disk



Printer

Note: All data are from Vention Lab.

SD/TF Card Slot


SD/TF card slot can only read/write one of the two cards at a time.



Compatible memory card:
Micro SD/Micro SDHC/Micro SDXC/SDHC/SDXC
Note: All data are from Vention Lab.

Gigabit Ethernet Port

Provides stable and fast connection to a wired network



Download
Lightning fast



Watch a film
Smooth



Play games
No latency

Note: All data are from Vention Lab.

Enjoy Music Anytime Anywhere


Connect the headphones/speaker to your
laptop through the 3.5mm audio port



Note: It is compatible with OMTP&CTIA earphones
but the microphone function is not supported.

Powerful Chip

Each function is carried by an independent chip, and the multi-function keeps stable and fluent when used at the same time.



Note: The chip/circuit board is rendered
and the internal structure is not fully displayed
Please refer to the actual product.

Plug & Play Drive Free

Compatible with Win 11/10/8/7/Vista/XP, Mac OS
Linux, iOS, Android OS and other operating systems.



Windows



Linux



Mac OS



iOS



Android OS



Compatible Devices

Support USB-C PC, laptop, phone with USB 3.1 Gen2 protocol and above

Laptop



MacBook



Lenovo



MateBook



HP



ASUS



Xiaomi



Dell



Other devices...

Tablet



iPad



MatePad



Surface



Other devices...

Mobile Phone



Huawei Mate40
Mate 40 Pro/20 X



Huawei P40
P40 Pro



Samsung S20/S10+
Note20



BlackShark 2/3
4/5/5 RS/5 Pro



Smartisan R1
Pro 2S



Other devices...



Part of Supported Models

Laptop

Apple	MacBook 12", MacBook Air 2018/2019/2020/2021 M1/M2, MacBook Pro 2016/2017/2018/2019/2020 2021/M1/M1 Pro/M1 Max/M2
Huawei	MateBook X/X Pro 19/20/21/22, MateBook E/E 2019 MateBook 13/13s/14/14s
Honor	MagicBook Pro 2019/2020, MagicBook 16/16 Pro
Xiaomi	Air12.5/13.3", Pro15.6", RedmiBookPro15 RedmiBook Pro 14, RedmiG, Xiaomi Pro14/15
HP	Pavilion x2, Spectre 13, EliteBook Folio G1, EliteBook 1050 G1, Envy 13, Omen 4/5/6/7, ProBook, EliteBook
ASUS	ZenBook 3/3 Pro, ZenBook X, U4100UN/U5100UQ ROG series, ProArt 16, TUF series
Dell	XPS13/15/17, G3/G5/G7/G15, Inspiron 5000/7000 Inspiron16 Plus, Alienware series
Lenovo	YOGA 6 Pro, ThinkPad X1 Carbon, Y7000/Y7000P Y9000K
Google	PixelBook
Razer	Blade/Blade Stealth
Microsoft	Surface Book 2, Surface GO

Mobile Phone

Samsung

Note8/9/20/20U, S8/S8+/S9/S9+/S10/S10+/S20/S20+
S21/S21U/FOLD3/FLIP3/S22/S22 Ultra

Huawei

Mate10/10 Pro/20/20 Pro/20 X/20 RS/30/30 Pro
Mate 30E Pro/Mate 30 RS/40/Mate 40E/40 Pro/40 Pro+
Mate 40 RS/Mate X2/Mate Xs, P20/P20 Pro/P30/P30 Pro
P40/P40 Pro/P50/P50 Pro/P50 Pocket

Smartisan

Nut R1/Pro 2S/R2

BlackShark

BlackShark 2/3/4/4 Pro/4S Pro/5/5 RS/5 Pro

OnePlus

7 Pro/8/8 Pro/9/9 Pro/10Pro

Asus

7 Pro/8/8 Pro/9/9 Pro/10Pro

Lenovo

Y90

Tablet

Apple

iPad Pro 2018/2020/2021, iPad Air 4 and Newer Model

Huawei

MatePad Pro 12.6" 2021, MatePad Pro 10.8" 2021
MatePad 11 2021

Microsoft

Surface Pro 7, Surface Pro X, Surface Go 2

Lenovo

Xiaoxin Pad 2021/2022, Xiaoxin Pad Pro 2021/2022
Yoga Pad Pro, Legion Y700

Game Console

Nintendo

Nintendo Switch

More USB-C models will be continuously updated

Note: Not compatible with Xiaomi/Redmi USB-C mobile phones

Delicate Design

Anti-Slip silicone pad

Stable and firmly



Aluminum alloy shell

Better heat emission

8 ° bevel design

Used as a laptop holder
to help it on cooling



Compact

Great for travel

Product Parameters

Brand	Vention
Name	12-in-1 USB-C Docking Station
Model	THSHC
Color	Gray
Interface	DP, HDMI, VGA, USB-C Gen 1
	USB 3.0*2, USB 2.0, RJ45
	SD/TF, TRRS 3.5mm, PD
Interface Technics	Nickel-Plated
Transmission Speed	5Gbps (USB-C Gen 1/USB 3.0)
	480Mbps (USB 2.0)
Resolution	4K@30Hz (HDMI/DP), 1080P@60Hz (VGA)
RJ45	1000Mbps
Conductor	Tinned Copper
Shell	Aluminum Alloy
Jacket	TPE
AWG	32AWG
OD	4.5mm±0.2mm
Length	0.25m±0.01m (Net length)
Rated Power	100W
Card Slot Type	2.0 SD 1-LUN
Compatible Memory Card	Micro SD/Micro SDHC/Micro SDXC
	SDHC/SDXC
Read & Write Simultaneously	Not Supported
Warranty	1 Year
Packing	Color Box



Packing Display



Note: Packing difference exists for different meters or batches.
The photo is for reference only



Multi-function 12-in-1 USB-C Docking Station

Technical Features		
Color	Gray	
Interface	USB-C/DisplayPort/HDMI/VGA/USB 3.2 Gen 1 Type-C/USB 3.0 x 2/USB 2.0/RJ45/SD/TF/3.5mm TRRS/PD	
Connector Process	Nickel-Plated	
Material	Aluminum alloy + ABS	
Data transfer rates	5Gbps (USB 3.2 Gen 1 Type-C/USB 3.0), 480Mbps (USB 2.0)	
Transmission rate	10/100/1000Mbps	
Card slot type	SD/TF 1-LUN (Read/Write only one card at a time)	
Card slot speed	USB 2.0	
Compatible audio standard	OMTP&CTIA	
Length	Art.No.	EAN Code
0.25m	THSHC	6922794768819
Package Contents		
Multi-function 12-in-1 USB-C Docking Station x 1		
Packaging Information		
Packing Dimension	33.2*10*2.4cm	
Packing Weight	0.335kg	
Carton Dimension	50*37*34cm	
Carton Qty	50pcs	
Carton Weight	17.75kg	



