VENTION
Innovation for life

8-in-1 USB-C Docking Station


8 Ports
Expansion
SD/TF
Card Slots
HDMI
4K@60Hz
Power Supply Port
100W Quick Charging
Ethernet Port
1000Mbps
VENTION 4K 60Hz
USB3.0 * 3
5Gbps

# Ultra HD 4K Visual Experience

4K@60Hz | 3D Video | HDR



VS

4K@60Hz 4K@30Hz

Note: The resolution and refresh rate are determined by the performance of your devices. If you intend to display 4K content, please make sure that both your input and output devices can support 4K. All data are from Vention Lab.

# Transfer Files in Seconds

**10X**
Faster than USB 2.0

USB 3.0 5Gbps

USB 2.0 480Mbps

Keyboard | Mouse | External Hard Drive | USB Drive

# 1000Mbps Fast and Stable than Wi-Fi

Smooth Gaming Experience

Fluid Video Playing

Download Files Faster

Stable Transmission

Note: All data are from Vention Lab.

PD 100W
Quick Charging
Around 1.5hrs 100%
MacBook Pro Fully Charged
Around 2hrs 100%
13" MacBook Fully Charged
Note: All data are from Vention Lab.

# Efficient SD/TF Card Slots

Note: Compatible Memory Cards: Micro SD/Micro SDHC/Micro SDXC/SDHC/SDXC.
All data are from Vention Lab.

# Advanced Chip

Note: The internal structure is a rendering.
Please refer to the actual product.


Superior Aluminum Alloy Shell
Anti-Fingerprint
Durable
Good Heat Dissipation
VENTION
4K 60Hz
VENTION

Compact & Portable
VENTION

Compact & Portable
VENTION

# Suitable for Various Scenarios

## Connect Phone

Expand your workplace

## Connect Tablet

E-learning helper

## Connect Switch

Immersive gaming experience

Note: You need to connect both the HDMI and power ports simultaneously.

# Universal Compatibility Plug-and-play

## Devices

MacBook Pro/Air

iPad Pro

Dell XPS

Galaxy

Switch

Surface

## HDMI Port

Television

Projector

Display

## Operating Systems

Windows

macOS

Linux

iPadOS

Android OS

# Compatibility List

## Laptop

| | |
|---|---|
| Apple | MacBook 12", MacBook Air 2018/2019/2020/2021 M1/M2, MacBook Pro 2016/2017/2018/2019/2020 2021/M1/M1 Pro/M1 Max/M2 |
| Huawei | MateBook X/X Pro 19/20/21/22, MateBook E/E 2019 MateBook 13/13s/14/14s |
| Honor | MagicBook Pro 2019/2020, MagicBook 16/16 Pro |
| Xiaomi | Air12.5/13.3", Pro15.6", RedmiBookPro15 RedmiBook Pro 14, RedmiG, Xiaomi Pro14/15 |
| HP | Pavilion x2, Spectre 13, EliteBook Folio G1, EliteBook 1050 G1, Envy 13, Omen 4/5/6/7, ProBook, EliteBook |
| ASUS | ZenBook 3/3 Pro, ZenBook X, U4100UN/U5100UQ ROG series, ProArt 16, TUF series |
| Dell | XPS13/15/17, G3/G5/G7/G15, Inspiron 5000/7000 Inspiron16 Plus, Alienware series |
| Lenovo | YOGA 6 Pro, ThinkPad X1 Carbon, Y7000/Y7000P Y9000K |
| Google | Pixelbook |
| Razer | Blade/Blade Stealth |
| Microsoft | Surface Book 2, Surface GO |

## Mobile Phone

| | |
|---|---|
| Samsung | Note8/9/20/20U, S8/S8+/S9/S9+/S10/S10+/S20/S20+ S21/S21U/FOLD3/FLIP3/S22/S22 Ultra |
| Huawei | Mate 10/10 Pro/20/20 Pro/20 X/20 RS/30/30 Pro Mate 30E Pro/Mate 30 RS/40/Mate 40E/40 Pro/40 Pro+ Mate 40 RS/Mate X2/Mate Xs, P20/P20 Pro/P30/P30 Pro P40/P40 Pro/P50/P50 Pro/P50 Pocket |
| Smartisan | Nut R1/Pro 2S/R2 |
| BlackShark | BlackShark 2/3/4/4 Pro/4S Pro/5/5 RS/5 Pro |
| OnePlus | 7 Pro/8/8 Pro/9/9 Pro/10Pro |
| Asus | 7 Pro/8/8 Pro/9/9 Pro/10Pro |
| Lenovo | Y90 |

## Tablet

| | |
|---|---|
| Apple | iPad Pro 2018/2020/2021, iPad Air 4 and Newer Model |
| Huawei | MatePad Pro 12.6" 2021, MatePad Pro 10.8" 2021 MatePad 11 2021 |
| Microsoft | Surface Pro 7, Surface Pro X, Surface Go 2 |
| Lenovo | Xiaoxin Pad2021/2022, Xiaoxin Pad Pro2021/2022 Yoga Pad Pro, Legion Y700 |

## Game Console

| | |
|---|---|
| Nintendo | Switch |

Tips: Only full-featured USB-C devices can handle data to its full function. Non-full-featured USB-C devices only support some extended functions.

# Specifications

| | |
|---|---|
| Brand | Vention |
| Name | 8-in-1 USB-C Docking Station |
| Model | TQK |
| Color | Gray |
| Output Interface | |
| HDMI | 4K@60Hz |
| 3 x USB 3.0 | 5Gbps |
| Ethernet Port | Gigabit RJ45 |
| Card Slot Type | SD/TF 1-LUN |
| | (Dual Cards Single Read) |
| Slot Rate Standard | USB 2.0 |
| PD Charge | 100W (Max) |
| Electroplating Process | Nickel-Plated |
| Conductor | Tinned Copper |
| Shell | Aluminum Alloy |
| Length | 0.15 m (Net cable length) |
| Warranty | 1 Year |
| Packing | Color Box |

Note: All data are from Vention Lab.
Sizes above are manually measured. There might be slight tolerance.

# Packaging Display

Note: Packing difference exists for different meters or batches.
The photo is for reference only.

# 8-in-1 USB-C Docking Station

| Technical Features | |
|---|---|
| Color | Gray |
| Interface | USB-C/HDMI/USB 3.0 x 3/RJ45/SD/TF/PD |
| Connector Process | Nickel-Plated |
| Material | Aluminum alloy + ABS |
| Data transfer rates | 5Gbps (USB 3.0) |
| Power supply | 100W PD |
| Resolution | 4K@60Hz |
| Transmission rate | 10/100/1000Mbps |
| Card slot type | SD/TF 1-LUN (Read/Write only one card at a time) |
| Card slot speed | USB 2.0 |

| Length | Art.No. | EAN Code |
|---|---|---|
| 0.15m | TQKHB | 6922794775121 |

| Package Contents |
|---|
| 8-in-1 USB-C Docking Station x 1 |

| Packaging Information | |
|---|---|
| Packing Dimension | 19*9.5*2cm |
| Packing Weight | 0.115kg |
| Carton Dimension | 48*29*30cm |
| Carton Qty | 90pcs |
| Carton Weight | 11.35kg |