

STYO/KTYO – HIGHLY FLEXIBLE ROUND BRAIDED COPPER CABLES

Construction and Application:

These braids are manufactured from annealed or tinned Cu-ETP wires. These wires are bunched together after the needed cross-section is calculated. Unlike the flexible braided tapes, bunches of wires are braided with machines that have 8/12 carries so that they have a round shape.



Technical Data:

Material: 0,05 mm - 0,20 mm annealed Cu ETP wires uncoated or tinned.

Delivery: plastic reels, in rings, on spools or wooden drums.

Cat. No.		Cross section	Wire diameter	Cable diameter	Weight
Bare copper	Tinned	[mm ²]	[mm]	[mm]	[kg/100m]
STYO-0250-10	KTYO-0250-10	2,5	0,1	2,4	2,2
STYO-0400-10	KTYO-0400-10	4	0,1	3,1	3,6
STYO-0600-10	KTYO-0600-10	6	0,1	4	5,4
STYO-1000-10	KTYO-1000-10	10	0,1	5	9,0
STYO-1600-10	KTYO-1600-10	16	0,1	6,3	14,3
STYO-2500-10	KTYO-2500-10	25	0,1	7,9	22,4
STYO-3500-20	KTYO-3500-20	35	0,2	9,7	31,4
STYO-5000-20	KTYO-5000-20	50	0,2	12	44,8
STYO-7000-20	KTYO-7000-20	70	0,2	14,5	62,7
STYO-9500-20	KTYO-9500-20	95	0,2	17	85,1