

SBO/KBO – FLEXIBLE ROUND STRANDED COPPER CABLES



Construction and Application:

These cables are manufactured out of wires that have a stronger diameters than 0,10 mm. They can be used for all applications where you need more mechanical stability than higher flexibility.

Technical Data:

Material: 0,15 mm - 0,85 mm annealed Cu ETP wires uncoated or tinned.

Delivery: plastic reels, in rings, on spools or wooden drums.

Cat. No.		Cross section	Wire diameter	Cable diameter	Weight
Bare copper	Tinned	[mm²]	[mm]	[mm]	[kg/100m]
SBO-0060-20	KBO-0060-20	6	0,2	4	5,4
SBO-0100-20	KBO-0100-20	10	0,2	4,5	9,0
SBO-0160-20	KBO-0160-20	16	0,2	5,8	14,3
SBO-0250-20	KBO-0250-20	25	0,2	7,5	22,4
SBO-0350-20	KBO-0350-20	35	0,2	9	31,4
SBO-0500-20	KBO-0500-20	50	0,2	11	44,8
SBO-0700-20	KBO-0700-20	70	0,2	13	62,7
SBO-0950-20	KBO-0950-20	95	0,2	15	85,1