

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

ECOR-3 relay base, for octal relay with 3 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Commercial data

Item number	2907520
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CKF314
Product key	CKF314
GTIN	4055626214375
Weight per piece (including packing)	70 g
Weight per piece (excluding packing)	67.01 g
Customs tariff number	85366990
Country of origin	CN

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Technical data

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition

Electrical properties

Nominal voltage U_N	400 V AC/DC
Nominal current I_N	10 A

Connection data

Input side

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)

Output side

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)

Dimensions

Width	38 mm
Height	75 mm
Depth Retaining bracket	84 mm (EL3-M52)

Material specifications

Color	traffic grey B (RAL 7043)
-------	---------------------------

Environmental and real-life conditions

Ambient conditions

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Mounting

Mounting type	DIN rail mounting
Mounting position	any

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2907520>



CSA
Approval ID: 255476



cUL Recognized
Approval ID: FILE E 113228



UL Recognized
Approval ID: FILE E 113228



EAC
Approval ID: RU C-DE.**08.B.01419

cULus Recognized

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Classifications

ECLASS

ECLASS-11.0	27371603
ECLASS-12.0	27371603
ECLASS-13.0	27371603

ETIM

ETIM 8.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

Mandatory accessories

REL-OR-BL/L-12DC/3X21 - Single relay

1109565

<https://www.phoenixcontact.com/gb/products/1109565>



Plug-in octal relay in basic design with power contacts, 3 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 12 V DC

REL-OR-BL- 24DC/3X21 - Single relay

1032532

<https://www.phoenixcontact.com/gb/products/1032532>



Plug-in octal relays in basic design with power contacts, 3 changeover contacts, test button, mechanical switch position indicator, polarity: A1+, A2-, input voltage: 24 V DC

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

REL-OR-BL/L-125DC/3X21 - Single relay

1109566

<https://www.phoenixcontact.com/gb/products/1109566>



Plug-in octal relay in basic design with power contacts, 3 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 125 V DC

REL-OR-BL/L- 24AC/3X21 - Single relay

1109567

<https://www.phoenixcontact.com/gb/products/1109567>



Plug-in octal relay in basic design with power contacts, 3 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 24 V AC

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

REL-OR-BL/L-115AC/3X21 - Single relay

1109568

<https://www.phoenixcontact.com/gb/products/1109568>



Plug-in octal relay in basic design with power contacts, 3 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 115 V AC

REL-OR-BL-230AC/3X21 - Single relay

1032537

<https://www.phoenixcontact.com/gb/products/1032537>



Plug-in octal relays in basic design with power contacts, 3 changeover contacts, test button, mechanical switch position indicator, input voltage: 230 V AC

Accessories

ECOR-3-BSC1/3X21 - Relay base



2907520

<https://www.phoenixcontact.com/gb/products/2907520>

DB 50- 90 BU - Wire bridge

2821180

<https://www.phoenixcontact.com/gb/products/2821180>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm^2 , loop length: 90 mm, ferrule length: 8 mm, color: blue



DB 50- 90 BK - Wire bridge

2820916

<https://www.phoenixcontact.com/gb/products/2820916>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm^2 , loop length: 90 mm, ferrule length: 8 mm, color: black



ECOR-3-BSC1/3X21 - Relay base

2907520

<https://www.phoenixcontact.com/gb/products/2907520>



DB 50- 90 GY - Wire bridge

2820929

<https://www.phoenixcontact.com/gb/products/2820929>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: gray



EL3-M52 - Relay retaining bracket

2833628

<https://www.phoenixcontact.com/gb/products/2833628>

Relay retaining bracket, wiring to suit relay base RIF-3 and PR3, for 52 mm high octal relay



ECOR-3-BSC1/3X21 - Relay base

2907520

<https://www.phoenixcontact.com/gb/products/2907520>



LDP3- 12- 24DC - Plug-in module

2833770

<https://www.phoenixcontact.com/gb/products/2833770>



Plug-in module, with freewheeling diode and yellow LED, polarity: **A1+**, **A2-**,
input voltage: 12 ... 24 V DC ± 20 %

V3-120-230UC - Plug-in module

2833945

<https://www.phoenixcontact.com/gb/products/2833945>



Plug-in module, with varistor, input voltage: 120 ... 230 V AC/DC ± 20 %

ECOR-3-BSC1/3X21 - Relay base

2907520

<https://www.phoenixcontact.com/gb/products/2907520>



RC3-120-230UC - Plug-in module

2833916

<https://www.phoenixcontact.com/gb/products/2833916>



Plug-in module, with RC element, input voltage: 120 ... 230 V AC/DC $\pm 20\%$

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk