

Extension cable (USB-A to mini USB) rc 1.4m black or 1.8m white

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1,4m or 1,8m / 20AWG – round cable
Maximum Load	60W
USB standard	USB2.0
Fast charge	N/A
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 37g / pc
Packing bunch	Various [pcs] 10

