

Extension cable (USB-A to micro USB) rc 1.4m

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.4m / 20AWG – round cable
Maximum Load	60W
USB standard	USB2.0
Fast charge	N/A
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 36g / pc
Packing bunch	Various [pcs] 10

