

Extension cable (USB-A to USB-C) rc 1.5m

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5 m / OD 4.5/50 2464 20ANG/2C+28ANG/30 Black/IC inside
Maximum Load	60W
USB standard	USB2.0
Fast charge	QC
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 48g / pc
Packing bunch	Various [pcs] 10

