

Extension cable (USB-C to USB-C) rc 1.5m apple white

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5 m / 2464 20AWG/20+28AWG/3C White PVC UL 0D 4.5mm
Maximum Load	60W
USB standard	USB2.0
Fast charge	PD/QC
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 57g / pc
Packing bunch	Various [pcs] 10

