

Illuminated pushbutton, Series 82, Ø 25 mm, flush, Silver,
IP65, IP67, Screw terminal

82-6152.1124



<https://eao.com/p/bb16a36c>

Your product:



82-6152.1124

Illuminated pushbutton, Series 82, Ø 25 mm, flush, Silver, IP65, IP67, Screw terminal

PRODUCT RANGE

HMI function:	Illuminated pushbutton
Series:	Series 82

FRONT

Front dimension:	Ø 25 mm
Front bezel colour:	Silver
Front bezel material:	Stainless steel

MOUNTING

Design:	flush
Mounting cut-out:	Ø 22 mm

OPERATING-/INDICATION PART

Shape of illumination:	Ring
Lens illumination:	illuminative
Lens colour:	Silver
Lens shape:	flush
Lens material:	Stainless steel
Lens optics:	opaque
Illumination colour:	Blue

ELECTRICAL CHARACTERISTICS

Electrical lifetime:	50 000 cycles of operation		
Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts) Service categorie AC-15 Voltage 24 VAC 35 VAC 110 VAC 220 VAC Switch rating DC service categorie DC-13 (Silver contacts) Voltage 24 VDC 35 VDC 110 VDC 220 VDC		
		Current	1 A
			1 A (M12 versio
			1 A
			0.5 A
		Current	0.7 A
			0.5 A (M12 vers
			0.2 A
			0.1 A
	according to UL 508 (Silver contacts) cosφ 0,75 ... 0,8 Voltage 120 VAC 240 VAC 24 VAC		
		Current	5 A
			3 A
			1 A
Lumi. Intensity:	mcd		
Operating voltage:	24 V AC/DC ±10 %		
Operation current:	7 mA		

MECHANICAL CHARATERISTIC

Tightening torque:	0.5 ... 0.6 Nm
Terminal:	Screw terminal
Contact material:	Silver
Switching action:	Momentary
Switching system:	Snap-action switching element
Total weight:	2.026 kg

AMBIENT CONDITION

IP front protection:	IP65, IP67
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Operating temperature:	– 30 °C ... + 70 °C

OTHER

max. number of switching elements:	1
Housing colour:	Silver

Housing material:	Stainless steel
Housing size:	19 mm
Symbol:	no symbol
Article number:	82-6152.1124