

Pushbutton with connector M12, Ø 22 mm, stainless steel 316L, Series 82, Ø 25 mm, flush, Silver, IP65, IP67, Cable 200 mm, 180°, Connector M12

82-665A.1000



<https://eao.com/p/5aead631>

Your product:



82-665A.1000

Pushbutton with connector M12, Ø 22 mm, stainless steel 316L, Series 82, Ø 25 mm, flush, Silver, IP65, IP67, Cable 200 mm, 180°, Connector M12

PRODUCT RANGE

HMI function: Pushbutton

Series: Series 82

FRONT

Front dimension: Ø 25 mm

Front bezel colour: Silver

Front bezel material: Stainless steel 316L

MOUNTING

Design: flush

Mounting cut-out: Ø 22 mm

OPERATING-/INDICATION PART

Lens colour: Silver

Lens material: Stainless steel 316L

Lens illumination: non illuminative

Lens shape: flush

Lens optics: opaque

ELECTRICAL CHARACTERISTICS

Electrical lifetime: 50 000 cycles of operation

Switching rating: 35 V AC/DC @ 0,5 A

MECHANICAL CHARACTERISTIC

Tightening torque: 0.5 ... 0.6 Nm

Terminal: Cable 200 mm, 180°, Connector M12

Terminal length cable: 200

Contact material: Silver

Switching action: Momentary

Switching system: Snap-action switching element

Total weight: 0.026 kg

AMBIENT CONDITION

IP front protection: IP65, IP67

Operating temperature: – 30 °C ... + 70 °C

Vibration resistance: 10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

OTHER

Housing colour: Silver

Housing material: Stainless steel

Housing size: 19 mm

Symbol: no symbol

Article number: 82-665A.1000