

DATASHEET

CABLE TIES SCREW FIXED
NATURAL



INSTALLATION TEMPERATURE	-10°C ÷ 60°C
MOISTURE ABSORPTION	2,7% (23°C - 50% R.H.)
FIRE RESISTANCE OF MATERIAL	UL 94-V2 Halogen-free
RESISTANCE TO	aromatic solvents, oils, greases and their derivatives
LIMITED RESISTANCE	acids
NON-RESISTANT	phenols and chlorinated solvents
WORKING TEMPERATURE	-40°C ÷ 85°C
MATERIAL	polyamide 6.6 natural

ITEM NO.	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
TTF4X150	3,6x150	natural	35	178
TTF5X200	4,6x200	natural	50	216