


RATING:16(8)A 125/250V~ (cURus/ ENEC15)
DIELECTRIC VOLTAGE-WITHSTAND:1,500VAC FOR 1 MINUTE
INSULATION RESISTANCE:DC 500V 100M Ω (MIN.)
CONTACT RESISTANCE:20m Ω INITIAL (MAX.)
WATERPROOF GRADE: IP68 (ABOVE THE PANEL)



REVISION	DESCRIPTION	REVISED BY	TOLERANCES			ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	DWG NO
			DRAWN BY	楊偉韶	DESIGNED BY	蔡劍	SCALE	2/1		MR2 SPEC DRAWING	S9105B
			CHECKED BY		APPROVED BY		DATE	2023.02.02	PART NO	MR2-110R2N-NBBQ-2ERC	
A	2023.06.13	依总表修正品名									
A	2023.02.02	首次出图									