






FOR DC Plug Size
2.1*5.5*9.5MM



ELECTRICAL CHARACTERISTIC

- | | |
|---|--|
| ① | CONTACT RESISTANCE: $\leq 30m\Omega$ |
| ② | INSULATION RESISTANCE: $\geq 2M\Omega$ |
| ③ | WITHSTAND VOLTAGE: DC100V |
| ④ | CURRENT RATING: 0.5A/DC100V |
| ⑤ | OPERATING TEMPERATURE: $-30^{\circ}C \sim 60^{\circ}C$ |

6	CRIMPING PATCH	BRASS
5	SOLDERING PATCH	BRASS
4	BODY	BRASS
3	PLASTIC HANDLE	PVC
2	DIELECTRIC	POM
1	PIN	BRASS


ITEM	DESIGNATION	MATERIAL
------	-------------	----------

RoHS
Compliant

APPD.
核准

DWG.
製圖 HELEN

DATE 制表日
2024/4/26



SCALE
比例 參考

UNIT
單位 MM

PAGE
張數 1 OF 1

TOLERANCE
容許公差
0 - 10 ±0.05
10 - 99 ±0.5
100 - 999 ±10.0
1000 - 9999 ±100.00
10000 - 99999 ±1000.00

SIZE
紙張尺寸 A4

REV.
版次 B

Ninigi

PART NAME 品名

2.1X5.5mm DC JACK
W/ PLASTIC HANDLE ROHS

PART NO.

料號 PC-GP2.1N