


1	2	3	4
A Empfohlener Ausschnitt fuer Rastbefestigung (Grat gegenueber Bestueckungsseite) <i>recommended cut-out for snap-in fixing ledge opposite to snap-in direction</i>	Wanddicke <i>wall thickness</i>	Ausschnittlaenge <i>length of cut-out</i>	Ausschnittbreite <i>width of cut-out</i>
	0.8 bis/ to 5	27.2 ± 0.1	12.2 ± 0.2



Flachstecker / *plug-in*
DIN 46244-A6.3-0.8

weiss
white
Wippe weiss
Zeichen schwarz
*rocker white
symbol black*

Aufschrift
Marking

155..
16(4)/250 ~ T100/55 T100
10(4)/250 ~ 5E4
5/100A 250V ~

05
16A 125-250V AC
1 HP 125V AC
2 HP 250V AC
R38

Herstellort/-jahr/-woche
code of manufacture: place/year/week

Auf Verpackung/ *on box* : G

Ausschalter 2-polig
Fuer Gerate der Klasse II geeignet

DPST
suitable for appliances of class II

G:Konform nach IEC 60335-1: 2001 Kap.30
G-matching IEC 60335-1: 2001 clause 30

fuer Form und Lage FOR SHAPE AND LOC.	☉ =		Allgemeintoleranzen UNTOLERANCED DIMENSIONS					Pause COPY	Blatt SHEET 01	TYP K	Zeichn./DRAWING NO. 15523122	Index				
				PROJEKTION	Abmasse und Nennmassbereiche Angaben in mm	0-6 >6-15 >15-30 >30-70 >70-120 >120	Laenge LENGTH ± 0.2 ± 0.4 ± 0.4 ± ± ±						Radien RADII ± 0.2 ± 0.3 ± 0.5 ± 10%			
fuer Winkel FOR ANGLE ± 2				ALL DIMENSIONS ARE IN MILLIMETRES					Original Din A4 Masstab SCALE 1 : 1 30mm	GERAETESCHALTER appliance switch						
									 MARQUARDT							
													CAD: NX V8.5 gez./DRAWN BY 04.06.14 MUT gepr./CHECKED BY Ersatz fuer/REPLACEMENT OF V05132302			
Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY		Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY										
		90093	04.06.14	MUT												