

Power USB-C Build-in Socket PD/QC without LED

Art. No. 67361050 (BP)

Art. No. 67361550 (SP)

25.07.2024

Input voltage: 8 - 30 V DC

Output USB-C:

Input Voltage	Output voltage	Output current max.
12,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
24,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
	15,0V	2,0A
	20,0V	1,5A

Power USB-C Build-in Socket PD/QC without LED

Art. No. 67361050 (BP)

Art. No. 67361550 (SP)

25.07.2024

Output power according to PD and QC protocol:

USB-C (PD): 30 W

Output power max.: 30 W

Charging protocol C-socket: Power Delivery (PD), Quick Charge, PPS

Current consumption: max. 5 mA (idle)

Protection against: short circuit, overload, overvoltage,
reverse polarity and overtemperature

Panel thickness: from 2 mm to 16 mm

Mounting hole: 28 mm (27,8mm)

Material:

Housing: ABS

Temperature load: max. 110 °C

Cable:

Stranded cable: 2 x 0,5 mm² red (+) / black (-)

Length: 150 mm

Power USB-C Build-in Socket PD/QC without LED

Art. No. 67361050 (BP)

Art. No. 67361550 (SP)

25.07.2024

