

Power USB-C Double Socket PD/QC

Art. No. 67371000 (BP)

Art. No. 67371500 (SP)

24.07.2024

Input voltage: 8 - 30 V DC

Output USB-C1:

Input Voltage	Output voltage	Output current max.
12,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
24,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
	15,0V	2,0A
	20,0V	1,5A

Output USB-C2:

Input Voltage	Output voltage	Output current max.
12,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
24,0V	5,0V	3,0A
	9,0V	3,0A
	12,0V	2,5A
	15,0V	2,0A
	20,0V	1,5A

Power USB-C Double Socket PD/QC

Art. No. 67371000 (BP)

Art. No. 67371500 (SP)

24.07.2024

USB-C1 and USB-C2 outputs are independent of each other, they can be used individually or together.

Output power according to PD and QC protocol:

USB-C 1,2 (PD):	30 W each
Output power max.:	2 x 30 W
Charging protocol C-socket:	Power Delivery (PD), Quick Charge, PPS
Current consumption:	max. 5 mA (idle)
Protection against:	short circuit, overload, overvoltage, reverse polarity and overtemperature
Control LED:	blue
Panel thickness:	from 2 mm to 16 mm
Mounting hole:	28 mm (27,8mm)

Material:

Housing:	Makrolon
Temperature load:	max. 130 °C

Cable:

Stranded cable:	2 x 0,5 mm ² red (+) / black (-)
Length:	150 mm

Power USB-C Double Socket PD/QC

Art. No. 67371000 (BP)

Art. No. 67371500 (SP)

24.07.2024

