

KIT SVITA E AVVITA DI PRECISIONE



118 mm



130 mm

45 PCS

CRV

M 2.5	M 5.5	T8	H 1.3	H 4.0	3.5	3.5
M 3.0	T3	T9	H 1.5	1.0	4.0	2.0
M 3.5	T4	T10	H 2.0	1.5	1.0	Y 2.0
M 4.0	T5	T15	H 2.5	2.0	1.5	U 2.6
M 4.5	T6	T20	H 3.0	2.5	2.0	0.8
M 5.0	T7	H 0.9	H 3.5	3.0	2.5	0.8

M.8775



