






FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



**L: MOMENTARY IS 38.4;
LATCHING IS 40.8.**



DOUBLE-BREAKPOINT SNAP-ACTION CONTACT SWITCH WITH FOUR TERMINALS



CONTACT COMPOSITION
1、 2、 3、 4 ARE ONE SET.
1,2 ARE NORMAL CLOSED(NC);
3,4 ARE NORMAL OPENED(NO).

PART NUMBER:GQ28-□■E/△/▲/S/※

"□"	CONTACT STRUCTURE
11	1NO1NC
22	2NO2NC

" "	OPERATION MODE
NO LETTER	MOMENTARY
Z	LATCHING

"Δ"	LAMP COLOR
R	RED
G	GREEN
Y	YELLOW
B	BLUE
W	WHITE

"▲"	LAMP VOLTAGE
6V	AC/DC 6V
12V	AC/DC 12V
24V	AC/DC 24V
110V	AC/DC 110V
220V	AC/DC 220V

	PROTECTION DEGREE
NO LETTER	IP65
FP	IP67(MOMENTARY)

**OTHER VOLTAGE CAN BE
MADE TO ORDER**

SPECIFICATIONS:

- 1.SWITCH RATING: Ui:250V, Ith:5A.
- 2.MECHANICAL LIFE: $\geq 1,000,000$ cycles.
- 3.ELECTRICAL LIFE: $\geq 50,000$ cycles.
- 4.CONTACT RESISTANCE: $\leq 50\text{m}\Omega$.
- 5.INSULATION RESISTANCE: $\geq 100\text{M}\Omega(500\text{VDC})$.
- 6.POWER-FREQUENCY WITHSTAND VOLTAGE: 1,500V, RMS 50Hz, 1min.
- 7.OPERATING TEMPERATURE: $-25^{\circ}\text{C} \sim +55^{\circ}\text{C}$ (NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).
- 8.OPERATING FORCE: ABOUT 4N(1NO1NC)/ABOUT 7.5N(2NO2NC).
- 9.OPERATING TRAVEL: ABOUT 2.5mm.
- 10.TORQUE: ABOUT 1.2N·m APPLIED TO NUT.
- 11.FRONT PANEL PROTECTION DEGREE: IP65(IP67 MOMENTARY CAN BE CUSTOMIZED), IK10.
- 12.TERMINAL TYPE: PIN TERMINAL(2.8X0.5mm).
- 13.GENERAL TOLERANCE:0-18mm ± 0.25 , 18-80mm ± 0.52 .
- 14.RoHS CAN BE CUSTOMIZED.
- 15.COMPLIANT WITH RoHS.

MATERIALS:

- 1.CONTACT: SILVER ALLOY.
2.BUTTON: STAINLESS STEEL/PC.
3.BODY: STAINLESS STEEL.
4.BASE: PA.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称		GQ SERIES ANTI-VANDAL PUSH BUTTON			
				UNIT 单位	mm
DWG NO. 图号		GQ28-E		SCALE 比例	1 : 1
				SIZE 图纸	A4
FILE NAME 档案名称		GQ28-E.DWG		DRAWN 制图	YDY 2023/12/22
				SHEET 张	1/1
				REV. 更改	1