



Click [here](#) for the 3D model.

Dimensions	
D	34mm MAX
H	24mm MAX
LL	5mm +/-2mm
S	21mm
S1	21mm
Wire Size	1.3mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	150
Typical Component Weight	42.5 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	2 mH (10 kHz)
Current	10 A
Temperature Range	-40/+120°C
DC Resistance	20 mOhms