




General Information	
Series	SN-JA
Style	Through-Hole
RoHS	Yes
Miscellaneous	21 (K) Temperature Rise Max.
Core	Fe

Specifications	
Inductance	60 uH (0.1MHz)
Current	8 A
Temperature Range	-40/+105°C
DC Resistance	0.021 Ohms

Click [here](#) for the 3D model.

Dimensions	
L	35mm MAX
T	19mm MAX
H	39mm MAX
LL	5mm +/-1.5mm
S	15mm NOM
Wire Size	1.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	200
Typical Component Weight	40.6 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.